




MDUSBC 2026-27 QUEENS



DISTANCE:	41 FEET	VOLUME:	28.9 mL
RATIO:	6.00:1	FORWARD:	15.2 mL
DROP BRUSH:	37 FEET	REVERSE:	13.7 mL
TANKS:	KEGEL & KEGEL	PUMP:	50 μ L



FORWARD LOADS DATA

#	START	STOP	LOADS	MICS	SPEED	DISTANCE	T.OIL
1	2L	2R	3	50	14	0 $\rightarrow$ 4	5,550
2	8L	8R	2	50	14	4 $\rightarrow$ 8	2,500
3	9L	9R	2	50	18	8 $\rightarrow$ 13	2,300
4	10L	10R	2	50	18	13 $\rightarrow$ 18	2,100
5	11L	11R	2	50	18	18 $\rightarrow$ 23	1,900
6	12L	12R	1	50	18	23 $\rightarrow$ 25	850
7	2L	2R	0	50	22	25 $\rightarrow$ 35	0
8	2L	2R	0	50	26	35 $\rightarrow$ 41	0


REVERSE LOADS DATA

#	START	STOP	LOADS	MICS	SPEED	DISTANCE	T.OIL
1	2L	2R	0	50	26	37 $\rightarrow$ 34	0
2	13L	13R	2	50	18	34 $\rightarrow$ 29	1,500
3	10L	10R	3	50	18	29 $\rightarrow$ 21	3,150
4	9L	9R	3	50	18	21 $\rightarrow$ 14	3,450
5	8L	8R	3	50	14	14 $\rightarrow$ 8	3,750
6	2L	2R	1	50	14	8 $\rightarrow$ 6	1,850
7	2L	2R	0	50	14	6 $\rightarrow$ 0	0

THIS PATTERN IS DESIGNED FOR:

DUAL CONDITIONING TANKS | REVERSE DROP BRUSH

This pattern may require adjustments if using a lane machine that does not have these features



KEGEL PATTERN LIBRARY APP



PATTERNLIBRARY.KEGEL.NET



SCAN QR CODE FOR
MORE PATTERNS ON
KEGEL PATTERN
LIBRARY

