




MDUSBC 2026-27 SERIES PATTERN 1



DISTANCE:	42 FEET	VOLUME:	27.6 mL
RATIO:	4.23:1	FORWARD:	17.1 mL
DROP BRUSH:	38 FEET	REVERSE:	10.5 mL
TANKS:	KEGEL & KEGEL	PUMP:	50 μ L



FORWARD LOADS DATA

#	START	STOP	LOADS	MICS	SPEED	DISTANCE	T.OIL
1	2L	2R	3	50	14	0 → 4	5,550
2	6L	6R	2	50	18	4 → 9	2,900
3	8L	8R	2	50	18	9 → 14	2,500
4	10L	10R	3	50	18	14 → 22	3,150
5	12L	12R	2	50	18	22 → 27	1,700
6	14L	14R	2	50	18	27 → 32	1,300
7	2L	2R	0	50	22	32 → 42	0


REVERSE LOADS DATA

#	START	STOP	LOADS	MICS	SPEED	DISTANCE	T.OIL
1	2L	2R	0	50	30	38 → 30	0
2	9L	9R	2	50	26	30 → 23	2,300
3	8L	8R	2	50	22	23 → 17	2,500
4	7L	7R	2	50	22	17 → 10	2,700
5	6L	6R	1	50	18	10 → 8	1,450
6	5L	5R	1	50	18	8 → 5	1,550
7	2L	2R	0	50	14	5 → 0	0

THIS PATTERN IS DESIGNED FOR:

DUAL CONDITIONING TANKS | REVERSE DROP BRUSH

This pattern may require adjustments if using a lane machine that does not have these features



SCAN QR CODE FOR
MORE PATTERNS ON
KEGEL PATTERN
LIBRARY



KEGEL PATTERN LIBRARY APP



PATTERNLIBRARY.KEGEL.NET